



Map 12: SpkrModel: 2-659A

RS02-8R-0659A-H

Notes

Revc=8.800 Ohm Fo=151.375 Hz Sd=2.376m MZMH=5.000 g  
 Bl=3.076 T# Qms=3.305 Qes=1.265 Qts=0.915 No=0.127 % SPLo=83.1 dB  
 Vas=479.121m Lr Cms=597.674u MIN Krm=273.663u Ohm Etm=0.939  
 Mms=1.850 g Mmd=1.783m Kg Kxm=8.043m H Exm=0.646

LMS 4-6-0-371 4月-14-2011

Person: Company:

Project: File: Untitled.lib

Sep 11, 2013 Wed 7:47 pm

L I N E A R X  
S Y S T E M S