



SPECIFICATIONS
 Current Rating: 1A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -40°C To +105°C
 Contact Resistance: 20 Milliohms Max.
 Insulation Resistance: 1000 Megohms Min.
 Withstanding Voltage: 500V AC/Min.
 Insulator: PBT+Glass Fiber,UL 94V-0
 Contact: Brass
 Finish: Gold Plated Over Nickel

Pos.	A	B
08	7.62	15.42
10	10.16	17.96
14	15.24	23.04
16	17.78	25.58
18	20.32	28.12
20	22.86	30.66
24	27.94	35.74
26	30.48	38.28
28	33.02	40.82
34	40.64	48.44
40	48.26	56.06

4UCON 元化興業股份有限公司
 4UCON TECHNOLOGY INC.

DRAWING No.		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE .X ±0.2 .XX ±0.10 ANG.
03771		MEI		
		CHECKED BY		
		BECKY		
		DRAWING BY		UNIT mm
		HZF		
SCALE	NONE	REV.	B0	

NO.	REV.	REVISIONS	CHK	DATE
△ B0		NEW RELEASE	BECKY	06/14/2006