




△ SPECIFICATION
 Current Rating:3 Amp
 Insulation Resistance:1000 Megaohms Min.
 Contact Resistance:20 Milliohms Max.
 Dielectric Withstanding:600V AC/DC
 Operation Temperature:-40°C~+105°C
 Contact:Phosphor Bronze,Gold Plated Over Nickel
 Insulator:PA6T UL94V-0,Black
 RoHS Compliant



Contacts	A	B	Contacts	A	B
2	5.08	2.54	22	56.38	53.34
3	7.62	5.08	23	58.92	55.88
4	10.66	7.62	24	61.46	58.42
5	13.2	10.16	25	64.0	60.96
6	15.74	12.70	26	66.54	63.50
7	18.28	15.24	27	69.08	66.04
8	20.82	17.78	28	71.62	68.58
9	23.36	20.32	29	74.16	71.12
10	25.9	22.86	30	76.7	73.66
11	28.44	25.40	31	79.24	76.20
12	30.98	27.94	32	81.78	78.74
13	33.52	30.48	33	84.32	81.28
14	36.06	33.02	34	86.86	83.82
15	38.6	35.56	35	89.4	86.36
16	41.14	38.10	36	91.94	88.90
17	43.68	40.64	37	94.48	91.44
18	46.22	43.18	38	97.02	93.98
19	48.76	45.72	39	99.56	96.52
20	51.3	48.26	40	102.1	99.06
21	53.84	50.80			

4UCON 元化興業股份有限公司
 4UCON TECHNOLOGY INC.

DRAWING No.		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE X. ±0.50 .X ±0.35 .XX ±0.25 .XXX ±0.05
06680		MEI		
		CHECKED BY	HZF	
		DRAWING BY	QQJ	
SCALE	NONE	REV.	A3	UNIT mm

△ A3	Del. Dim. 7.70	HZF	08/17/2010
△ A2	Modify Data	HZF	01/06/2010
△ A1	Modify Data	HZF	12/22/2009
△ A0	NEW RELEASE	SHIN	08/14/2006
NO. REV.	REVISIONS	CHK	DATE