



8 40mm



8 50mm



8 60mm



8 100mm



4 140mm




4 160mm



8 200mm




4 300mm



10
90° Bracket



120
Socket head cap screw
M3 x 5mm w lock washer



20
Joining Plate "L"



60
Nut Plate



20
Vinyl Cap