
## **PCB**




PCB Material: FR-4 (Hitachi Chemical: MCL-E-67), t = 0.8mm



Data format = RS274X

## Parts Layout





## Parts List



Reference	Parts Name	Size[mm]	Value	Tolerance	Vendor
C1	GRM1552C1H5R0WA01D	1.0x0.5	5.0pF	±0.05pF	Murata
C2	GRM1552C1H5R0WA01D	1.0x0.5	5.0pF	±0.05pF	Murata
C3	GRM1552C1H5R0WA01D	1.0x0.5	5.0pF	±0.05pF	Murata
C4	GRM1552C1H5R0WA01D	1.0x0.5	5.0pF	±0.05pF	Murata
C5	GRM1552C1H2R4WA01D	1.0x0.5	2.4pF	±0.05pF	Murata
C6	GRM1552C1H2R4WA01D	1.0x0.5	2.4pF	±0.05pF	Murata
L1	LQW18AS24NG00D	1.6x0.8	24nH	±2%	Murata
L2	LQW18AS24NG00D	1.6x0.8	24nH	±2%	Murata
L3	LQW15NA19NG00D	1.6x0.8	19nH	±2%	Murata
L4	LQW18AS11NG00D	1.0x0.6	11nH	±2%	Murata
L5	LQW18AS11NG00D	1.6x0.8	11nH	±2%	Murata
R1	CR10-432FV	1.0x0.5	4.3kΩ	±1%	HDK
CN1	CONREVSMA003.031				Linx Technologies