



1	FREQUENCY :	Center Frequency 868MHz	6	IMPEDANCE :	50 Ω
2	GAIN :	2dBi	7		
3	V.S.W.R :	≤1.5	8		
4	LENGTH :	L105xW10xH10 mm	9		
5	CONNECTOR :	SMA PLUG RP	10		