



2228AG
(Phosphor Bronze)



2228BG
(Brass)



2228CG
(Brass)

C
Specificatipns:
Current Rating:3.0A AC,DC
Voltage Rating:500V AC,DC
Contact Resistance:30m ohm Max
Insulation Resistance:5000M ohm Min
Withstanding Voltage:650V AC/minute
Operating Tenperature Range:−40°C~+105°C
Material:
Insulator Material:PBT (UL94V−0)
Contact Material:Copper Alloy
Finish:Gold Plated

2228AG=4.5mm Length Open Type (BK)
2228BG=6.47mm Length Gth Close Type (BK,BU,RD,YL,WH,GN)
2228CG=5.97mm Length Open Type (BK,BU,RD,YL,WH,GN)
2228DG=8.0mm Length Open Type (BK)
2228EG=8.5mm Length Close Type (BK)
2228GG=13.5mm Length W/Handle (BK) D
13.65mm Length W/Handle (BU,RD,YL,WH,GN)

How to order
2228XG−XX

- Insulator color
  - Standard Black Color
  - BU=blue
  - RD=red
  - YL=yellow
  - WH=white
  - GN=green
- Type
  - A/B/C/D/E/G



2228DG
(Phosphor Bronze)



2228EG
(Phosphor Bronze)



2228GG(Brass)
(Material:Nylon 66)

ROHS Compliant

REV	DATE	FILE	BY
E			
D	06−Feb−2020	modify 2228GG Length	Romina
C	27−Mar−2014		Cherry
B	02−Jan−2006		Wendy
A	02−Jul−2004		Cel king

DRAWN: Cel king
CHECKED: ANT
APPROVAL: Mike Wu

GENERAL TOLERANCE:
X.X=±0.2
X.XX=±0.15

UNIT: MM
SCALE:
SHEET: 1 / 1
PROJECTION:

Neltron Connectors **Neltron Industrial Co., Ltd.**

DESCRIPTION: 2.54mm Mini Jumper
PART NO: 2228XG−XX
SIZE: A4