



1	FREQUENCY : 810-910 MHz	6	IMPEDANCE : 50 Ω
2	GAIN : 2dBi	7	
3	V.S.W.R : ≤ 2.5 (Center Frequency 868MHz < 1.5)	8	
4	ANTENNA LENGTH : L200xW13.1xH13.1 mm	9	
5	CONNECTOR : SMA PLUG RP	10	