


REV	ECRN	DATE
1	NEW PRODUCTION	20221022



- NOTES:
- 1.ELECTRICALTTEST:100%OPEN,SHORT&MIS WIRE TEST.
 - 2.CONTACT RESISTANCE:2 ohm,
 - 3.INSULATOR RESISTANCE:5M ohm.
 - 4.HIGH VOLTAGE:DC 300V 0.01sec.
 - 5.MUST BE ROHS COMPLIANT.

接线表

P1	P2	P3	P4	P5
VBUS — RED	1(+5V) — RED	1 — RED	1 — RED	VBUS — RED
A5 — 5.1KΩ				A5 — 56KΩ
A7 — WHITE	2(DM) — WHITE	2 — WHITE	2 — WHITE	A7 — WHITE
A6 — GREEN	3(DP) — GREEN	3 — GREEN	3 — GREEN	A6 — GREEN
GND — BLACK	5(GND) — BLACK	4 — BLACK	5 — BLACK	GND — BLACK
SHELL — SHELL	SHELL — SHELL	SHELL — SHELL	SHELL — SHELL	SHELL — SHELL

NO.	PART NO	ITEM	DESCRIPTION	Q' TY	UNIT
⑪	B.01012M.0N06R	CONNECTOR	USB TYPE-C M PIN GODED SHELL PLATED NICKEL PLASTIC:BLACK 56KΩ	1	PCS
⑩	I.000000.0400R	TIE	L=100mm COLOR BLACK	1	PCS
⑨	J.000008.0500R	TIN WIRE	TIN WIRE OD:0.8MM	8.5	G
⑧	C.060P03.0100R	MOLDING	PVC 60P RED	35.5	G
⑦	C.000000.0000R	MOLDING	PE	5.5	G
⑥	J.032014.0900R	PCB	USB ROOT HUB PCB L=32MM W=14.7MM	1	PCS
⑤	B.01004M.0N03R	CONNECTOR	USB B/M PIN GOLD PLATED SHELL NICKEL PLASTIC WHITE	1	PCS
④	B.02005M.0N00R	CONNECTOR	MINI USB 5P PIN GOLD PLATED SHELL NICKEL PLASTIC BLACK	1	PCS
③	B.03005M.0N00R	CONNECTOR	MICRO USB 5P PIN GODED PLATED SHELL NICKEL PLASTIC:BLACK	1	PCS
②	B.01012M.0N06R	CONNECTOR	USB TYPE-C M PIN GODED SHELL PLATED NICKEL PLASTIC:BLACK 5.1KΩ	1	PCS
①	A.011X03.0400R	CABLE	UL2725 28AWG(7/0.12TC)*1P(WHITE, GREEN)+28AWG(7/0.12TC)*2C(RED, BLACK) AL+D(7/0.12TC)+B(32/0.10TCAAM)JACKET PVC 60P RED OD=4.0±0.1mm L=1800MM L=355MM	1	PCS

RoHS COMPLIANT		朋联电子有限公司 DongGuan PengLian Electronics Co.,Ltd TEL:076938835098/38835095 FAX:076938835091	
DRAWN BY		比例: FREE	TITLE: TYPE-C M TO MINI 5P+MICRO+BM
CHECKED BY		單位: mm	SUPPLIER`S ITEM: 9.00ACCA3699.000R
APPROVED BY			CUSTOMER: Spark Fun
			CUSTOMER`S ITEM: 21049
		DRAWING NO. ACCA-3699	DATE 2022.10.22