



**△ SPECIFICATION**

Current:1A  
 Dielectric Strength:1000V AC Minute  
 Contact Resistance:20 Milliohms Max.  
 Insulation Resistance:5000 Megaohms Min.  
 Operation Temperature:-55°C~+105°C  
 Housing:PA6T(UL94V-0),Black  
 Contact:Brass,Gold Flash Over Nickel  
 No. Of Contacts:04~100 Contacts  
 RoHS Compliant

**4UCON** 元化興業股份有限公司  
 4UCON TECHNOLOGY INC.

DRAWING No.		APPROVED BY		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE .X ±0.38 .XX ±0.25 ANG. ±5°
00140		EMILY		
		CHECKED BY		
		HZF		UNIT mm
		DRAWING BY		
		HAO		NO. REV.
SCALE	NONE	REV.	A4	

△ A4	Modify Spec.	HZF	05/23/2015
△ A3	Modify Data	HZF	04/15/2013
△ A2	Modify Data	HZF	11/28/2012
△ A1	Modify Data	HZF	08/02/2010
△ A0	NEW RELEASE	BECKY	08/08/2005
REVISIONS		CHK	DATE