



REV	ECRN	DATE
1	NEW PRODUCTION	20190528



P/N	L(mm)	T(mm)	Cutting line size(mm)	朋联料号
	300	10	300	9.00ACCA2532.003R
	800	10	800	9.00ACCA2532.008R
	2000	30	2000	9.00ACCA2532.020R

- NOTES:
- 1.ELECTRICAL TEST:100%OPEN,SHORT&MIS WIRE TEST.
  - 2.CONTACT RESISTANCE:2 ohm,
  - 3.INSULATOR RESISTANCE:5M ohm.
  - 4.HIGH VOLTAGE:DC 300V 0.01sec.
  - 5.MUST BE ROHS COMPLIANT.



接线表

P1		P2	
1	RED	A4+A9+B4+B9	VCC
2	WHITE	A7 D-	
3	GREEN	A6 D+	
4	DRAIN	A1 A12 B1 B12	GND
	BRAID	SHELL	SHELL

NO.	PART NO	ITEM	DESCRIPTION	Q'TY	UNIT
	I.000001.0400R	TIE	L=100mm COLOR BLACK	1	PCS
⑥	J.000008.0500R	TIN WIRE	TIN WIRE OD:0.8MM	2.5	G
⑤	C.085P01.0200R	MOLDING	TPE 85A BLACK	10	G
④	C.0000P00.0000R	MOLDING	PE	3	G
③		CONNECTOR	USB 2.0 TYPE C/M GOLDDED PLATED SHELL NICKEL PLASTIC:BLACK 56.0KΩ	1	PCS
②	B.01004M.0N01R	CONNECTOR	USB A/M 4P PIN GOLDDED PLATED SHELL NICKEL PLASTIC: WHITE Double sided insert	1	PCS
①		CABLE	NO UL32AWG (11/0.06TS)*2C+23AWG (98/0.0.06TS)*1C+D (41/0.08TS)*1C+AL+B(16/4/0.08TS) JACKET TPE 65A BLACK OD:2.8MM	1	PCS

RoHS COMPLIANT		朋联电子有限公司 DongGuan PengLian Electronics Co.,Ltd TEL:076938835098/38835095 FAX:076938835091	
比例:	FREE	TITLE: USB 2.0 A/M TO USB 2.0 TYPE C	
单位:	mm	SUPPLIER`S ITEM: 9.00ACCA2532.XXXR	
CHECKED BY		CUSTOMER: SPARK FUN	
APPROVED BY		CUSTOMER`S ITEM:	
		DRAWING NO.	ACCA-2532
		DATE	2019.05.28