


| REV | ECRN           | DATE     |
|-----|----------------|----------|
| 1   | NEW PRODUCTION | 20190218 |
|     |                |          |
|     |                |          |


P1

P2



packaging :



RED\*2PCS, WHITE\*2PCS, BLACK\*2PCS, GREEN\*2PCS, YELLOW\*2PCS



NOTES:

1. ELECTRICAL TEST: 100% OPEN, SHORT & MIS WIRE TEST.
2. CONTACT RESISTANCE: 1 ohm.
3. INSULATOR RESISTANCE: 5M ohm.
4. HIGH VOLTAGE: DC 300V 0.01sec.
5. MUST BE ROHS COMPLIANT.

|     |                |           |  |       |      |
|-----|----------------|-----------|--|-------|------|
| ⑥   |                |           |  |       |      |
| ⑤   | I.100150.0300R | PE BAG    | 200*150*0.04MM RED edge chain bag  | 1     | PCS  |
| ④   | D.00254M.1400R | TERMINAL  | Cold pressed terminal red sheath FDD 5.5-250   | 10    | PCS  |
| ③   | J.000008.0500R | TIN WIRE  | TIN WIRE OD:0.8MM  | 1.5   | G    |
| ②   | J.000202.1100R | CONNECTOR | TOOL HOLDER:025/026/027 COLOR: RED, WHITE, BLACK, GREEN, YELLOW L=30MM                                     | 10    | PCS  |
| ①   |                | CABLE     | UL1007 24AWG(10/0.16BC)*1C JACKET: PVC 60P COLOR: RED, WHITE, BLACK, GREEN, YELLOW )OD: 1.5±0.15MM L=180MM | 10    | PCS  |
| NO. | PART NO        | ITEM      | DESCRIPTION  | Q' TY | UNIT |

|                |  |     |  |   |   |
|----------------|--|-----|--|---|---|
| RoHS COMPLIANT |  |     |  <b>朋联电子有限公司</b><br>DongGuan PengLian Electronics Co.,Ltd<br>TEL:076938835098/38835095 FAX:076938835091 |   |   |
| DRAWN BY       |  | 袁小政 | 20190218   | 比例: FREE  | TITLE: TOOL HOLDER TO 250 cold-press terminal |
| CHECKED BY     |  |     |  | 单位: mm  | SUPPLIER`S ITEM: 9.00ACCA2438.000R            |
| APPROVED BY    |  |     |  |  | CUSTOMER: SPRAK FUN                           |
|                |  |     | DRAWING NO. ACCA-2438  |   | DATE 2019.02.18                               |