

9g plastic teeth micro servo

Model number: RM001-S

Weight: 9g

Dimensions: 23.1 x 11.9 x 26.0 mm

Torque: 1.2kg/cm (at 4.8V) 1.5kg/cm (at 6V)

Speed: 0.11sec/60 ° (at 4.8V) 0.09sec/60 ° (at 6V)

Motor type: iron core

Gear type: plastic

Working voltage: 4.8v-6v

Operating temperature: 0 °C - 60 °C

Standard signal: 1000~2000 microseconds

Rotation: 180 degrees

Current: < 500mA

Line length: 180mm

Deadband setting: 4 usec

