



**Legend:**

- |          |                |   |           |
|----------|----------------|---|-----------|
| ■ Power  | Ⓜ Power Input  | ■ GPIO Digital External                         | Ⓜ LED     |
| ■ Ground | Ⓜ Power Output | □ Analog External                               | Ⓜ RGB LED |
|          |                | ■ Main Part                                     | □ Other   |
|          |                | ■ Secondary Part                                |           |
|          |                | ■ Internal Component                            |           |
|          |                | ■ Other Pins (Reset, System Control, Debugging) |           |

- ⚠️ **WARNING** Ensure the correct polarity is respected before connecting the device to the power supply
- ⚠️ **MAXIMUM** analogic input voltage is 10V
- ⚠️ **MAXIMUM** relay rated voltage 250VAC  
**MAXIMUM** current per relay 10A



SKU code: AFX00003  
Full Pinout - Page 1 of 1  
Last update: 7 Mar, 2023

**DOCS . ARDUINO . CC**

This work is licensed under the Creative Commons Attribution-ShareAlike 4.0 International License. To view a copy of this license, visit <http://creativecommons.org/licenses/by-sa/4.0/> or send a letter to Creative Commons, PO Box 1866, Mountain View, CA 94042, USA.