




GNSS Antenna Module



SIM33ELA

SIMCom presents a high performance GPS module accompany with GNSS antenna-SIM33ELA. This is a standalone GNSS module embedded a linear antenna . Designed with MTK's high sensitivity navigation engine, it allows you to achieves the industry's highest levels of sensitivity, accuracy, and Time-to-First-Fix (TTFF) with lowest power consumption. And with embedded antenna in SMT type, it is very easy to embed into customer's application.

Smart Machine Smart Decision

Mechanical data

- Dimensions: 14*9.6*2.15mm
- Weight: 0.5g

Features

- Support GPS/GLONASS/Galileo/QZSS
- Support EASY™ self-generated orbit prediction
- Support EPO™ orbit prediction
- Support AGPS
- Support SBAS ranging (WAAS, EGNOS, GAGAN, MSAS)
- Support Jamming Removing
- Low-noise amplifier has been integrated

Interfaces

- Serial interfaces UART
- Digital I/O PPS
- 3D-FIX
- FORCE -ON
- Protocols NMEA
- PMTK

Support product

- SIM68 EVB KIT with USB V2.0 full speed interface

Performance data

- Receiver type 33tracking/99 acquisition-channel GNSS receiver
- Max. update rate 10Hz
- Sensitivity¹
 - Tracking: -165 dBm
 - Reacquisition: -160 dBm
 - Cold starts: -147 dBm
- Time-To-First-Fix²
 - Cold starts: 28 s (typical)
 - Warm starts: 26s
 - Hot starts: <1s
 - EPO Assist: 13s (CTTFF)
- Accuracy
 - Automatic Position³: 2.5m CEP
 - Speed⁴: 0.1m/s
- Operation temperature: -40°C ~+85 °C

Electrical data

- Power supply 2.8~4.3V
- Backup power 2.0V~4.3V
- Power consumption²
 - Acquisition 25mA
 - Tracking 20mA
 - Backup 14uA

- 1.Demonstrated on EVB KIT at library
- 2.All SV @ -130 dBm
- 3.50% 24 hr static, -130dBm
- 4.50% @ 30m/s

Distributed by:



More about SIMCom SIM33ELA
Please contact:
Tel: 86-21-32523300
Fax: 86-21-32523301
Email: simcom@sim.com
Website: www.sim.com

The Netherlands



Elektrostraat 17
NL-7483 PG Haaksbergen

T: +31 (0)53 573 33 33
F: +31 (0)53 573 33 30
E: nl@texim-europe.com

Belgium



Zuiderlaan 14 bus 10
B-1731 Zellik

T: +32 (0)2 462 01 00
F: +32 (0)2 462 01 25
E: belgium@texim-europe.com

UK & Ireland



St. Mary's House, Church Lane
Carlton Le Moorland
Lincoln LN5 9HS

T: +44 (0)1522 789 555
F: +44 (0)845 299 22 26
E: uk@texim-europe.com

Germany North



Bahnhofstrasse 92
D-25451 Quickborn

T: +49 (0)4106 627 07-0
F: +49 (0)4106 627 07-20
E: germany@texim-europe.com

Germany South



Martin-Kollar-Strasse 9
D-81829 München

T: +49 (0)89 436 086-0
F: +49 (0)89 436 086-19
E: germany@texim-europe.com

Austria



Warwitzstrasse 9
A-5020 Salzburg

T: +43 (0)662 216 026
F: +43 (0)662 216 026-66
E: austria@texim-europe.com

Nordic region



Sdr. Jagtvej 12
DK-2970 Hørsholm

T: +45 88 20 26 30
F: +45 88 20 26 39
E: nordic@texim-europe.com

General information



info@texim-europe.com
www.texim-europe.com