



1	FREQUENCY :	Center 433 MHz	6	IMPEDANCE :	50 Ω
2	GAIN :	2dBi	7		
3	V.S.W.R :	≤1.6:1	8		
4	ANTENNA LENGTH :	L200×W13.1×H13.1 mm	9		
5	CONNECTOR :	SMA PLUG	10		