


3V Lithium Manganese Dioxide Button Cell Data Sheet

Dimensions(mm)




Property:

Normal Voltage: 3V
Nominal Capacity: 125mAh
Recommended Continuous Drain: 0.2mA
Recommended Pulse Drain: 10mA
Standard Load: 30k Ω

Discharge Characteristics on Load

Voltage(V)


At 20 $^{\circ}$ C



Discharge Characteristics on Temperature

Voltage(V)

Load 30k Ω



CR1632