

WE 1010, 120V

Product no.: WE1010NA



Benefits

For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning




Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	150 x 120 x 98
Dimensions L x W x H (inches)	5.91 x 4.72 x 3.86
Weight (approx.) in kg	1.4
Voltage	120 V
Power	85 W
Channels	1
Temperature range (depends on tool) °C	100 - 450
Temperature range (depends on tool) °F	200 - 850
Temperature accuracy °C	Average tip temperature can be „offset“ to +/- 5°C at idle with no load
Temperature accuracy °F	Average tip temperature can be „offset“ to +/- 9°F at idle with no load
Temperature stability °C	± 6
Temperature stability °F	± 10
Equipotential bonding socket	---
Display	Digital LC Display
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE