





SPECIFICATION

Current Rating:3 Amps

- △△ Withstand Voltage:1000V AC Min./Minute
- △△ Contact Resistance:20 Milliohms Max.
- Insulation Resistance:1000 Megaohms Min.
- Operation Temperature:-40°C~+105°C
- Contact:Brass,Gold Flash Over Nickel
- Insulator:PA6T(UL94V-0),Black
- RoHS Compliant



△ Recommended P.C.B. Layout(Top View)
(PCB Board Tolerance±0.05)



4UCON 元化興業股份有限公司
4UCON TECHNOLOGY INC.

DRAWING No.

00548

APPROVED BY

EMILY

CHECKED BY

HZF

DRAWING BY

SAN

SCALE

NONE

REV.


A2

UNLESS OTHERWISE
SPECIFIED
TOLERANCES ARE

X. ±0.25	X.* ±2°
.X ±0.20	.X* ±1.5°
.XX ±0.15	.XX* ±1°
.XXX ±0.10	.XXX* ±0.5°

UNIT

mm



NO.	REV.	REVISIONS	CHK	DATE
△2	A2	Modify Data	HZF	11/06/2021
△1	A1	Modify Data	HZF	05/28/2014
△0	A0	NEW RELEASE	HZF	04/04/2013