


SK40 Tight Buffer, Polyethylene



The Light Connections PE tight buffer is composed of a fiber and a Polyethylene outer jacket. All component materials meet the EU RoHS and REACH Directive standards.



Product Specifications

Storage Temp. (C°) Operating Temp. (C°)
-40 / +70 -20 / +70

Jacket Characteristics

TLC Part Number	Jacket Material	Fiber Count	Nominal Dimension	Weight lbs. / Km	Bend Radius (cm) Install / Operate
P96TB01TEBL2.2	Polyethylene Black	1	2.2mm	5	3.3/2.2

Optical Characteristics

Fiber Type	Core Size	Outer Diameter	Attenuation
SK40 (Plastic Fiber)	0.96	1.0mm	-



Address: 1532 Centre Pointe Dr. Milpitas, CA 95035
 Phone : 408-945-6613
 Fax : 408-273-6592
 Email : sales@fo4sale.com
 On the web : www.fiberoptics4sales.com

REV-3.0 Date- 12/16/09

Supersedes REV- 2.0 Date- 10/16/09