


REV	ECRN	DATE
1	NEW PRODUCTION	20211108



NOTES:

1. ELECTRICAL TEST: 100% OPEN, SHORT & MIS WIRE TEST.
2. CONDUCTOR RESISTANCE: 2MΩ
3. INSULATOR RESISTANCE: 5M ohm.
4. HIGH VOLTAGE: DC 300V 0.01sec.
5. MUST BE ROHS COMPLIANT.

PIN WIRING

P1		P2
1	RED	1
2	WHITE	2
3	BLACK	3

NO.	PART NO	ITEM	DESCRIPTION	Q' TY	UNIT
⑤	I.000001.0400R	TIE	TIE BLACK L=100MM	1	PCS
④	J.000008.0500R	TIN WIRE	OD:0.8MM	2.5	G
③	C.040P00.0100R	MOLDING	PVC 45P BLACK	9.5	G
②	B.04035M.0N03R	CONNECTOR	DC3.5*6.0 3-POLE MALE SHELL NICKEL PLASTIC:BLACK	2	PCS
①	A.000X01.0310R	CABLE	NO-UL 28AWG(7/0.12TC)*3C (red,black,white) OD:3.5mm±0.1MM JACKET:PVC BLACK L=1010MM	1	PCS

RoHS COMPLIANT			东莞市博帆科技有限公司			
DRAWN BY 刘骏驰 20211108			DongGuan BoFan Electronics Co.,Ltd TEL:076938835098/38835095 FAX:076938835091			
CHECKED BY			比例: FREE	TITLE: DC3.5 3-POLE M TO DC3.5 3-POLE		
APPROVED BY			單位: mm	SUPPLIER'S ITEM: 9.00ACCA3382.000R		
			CUSTOMER: sparkfun			
			CUSTOMER'S ITEM:			
			DRAWING NO. ACCA-3382	DATE	2021.11.08	