



Barometer - LPS28DFW

Voltage Input Range:
1.7V - 3.6V




Connectors

PTH connectors only
accept 22AWG or smaller



Test Points




Power LED

Cut trace
disconnec
power LE




I2C Pullups



Cut traces to disconnect I2C pullup resistors

I2C Address Selection

I2C Address	
3V3	0x5D
GND	0x5C (Default)



Released under the Creative Commons Attribution Share-Alike 4.0 License
<https://creativecommons.org/licenses/by-sa/4.0/>



TITLE: SparkFun_Qwiic_Micro_Barometer_LPS28DFW

Design by: Dryw Wade

REV:
v10

Date: 11/17/2022 3:43 PM

Sheet: 1/1