

MAX98357A




Jumpers


Stereo Output Channel Select



Mono Output (Default) (Left/2 + Right/2)



Connector



| Gain Selection | |
|---------------------------------------|--------|
| GAIN_SLOT | GAIN |
| Connect to GND through 100kΩ resistor | +15 dB |
| Connect to GND | +12 dB |
| Unconnected (Default) | +9 dB |
| Connect to VDD | +6 dB |
| Connect to VDD through 100kΩ resistor | +3 dB |





Released under the Creative Commons Attribution Share-Alike 4.0 License https://creativecommons.org/licenses/by-sa/4.0/

TITLE: SparkFun_I2S_Audio_Breakout

Design by: Alex Wende

REU: v10

0088

Date: 8/29/2018 1:57 PM

Sheet: 1/1