

REV	ECRN	DATE
1	NEW PRODUCTION	20250213

P1

152±5

5±2 tinning

① ② ③

NOTES:

1.ELECTRICAL TEST:100%OPEN,SHORT&MIS WIRE TEST.

2.CONTACT RESISTANCE:2 OHM MAX,

3.INSULATOR RESISTANCE:5M OHM MIN.

4.MUST BE ROHS COMPLIANT.

④ TO BE ASSEMBLED TO THE CABLE

Circuits	Model No.		Dimensions (mm)			Q'ty / reel
	Top entry type	Side entry type	A	B		
				Top entry type	Side entry type	
2	B2B-PH-SM4-TB	S2B-PH-SM4-TB	2.0	7.95	7.9	1,000
3	B3B-PH-SM4-TB	S3B-PH-SM4-TB	4.0	9.95	9.9	1,000
4	B4B-PH-SM4-TB	S4B-PH-SM4-TB	5.0	11.95	11.9	1,000
5	B5B-PH-SM4-TB	S5B-PH-SM4-TB	6.0	13.95	13.9	1,000
6	B6B-PH-SM4-TB	S6B-PH-SM4-TB	10.0	15.95	15.9	1,000
7	B7B-PH-SM4-TB	S7B-PH-SM4-TB	12.0	17.95	17.9	1,000
8	B8B-PH-SM4-TB	S8B-PH-SM4-TB	14.0	19.95	19.9	1,000
9	B9B-PH-SM4-TB	S9B-PH-SM4-TB	16.0	21.95	21.9	1,000
10	B10B-PH-SM4-TB	S10B-PH-SM4-TB	18.0	23.95	23.9	1,000
11	B11B-PH-SM4-TB	S11B-PH-SM4-TB	20.0	25.95	25.9	1,000
12	B12B-PH-SM4-TB	S12B-PH-SM4-TB	22.0	27.95	27.9	1,000
13	B13B-PH-SM4-TB	S13B-PH-SM4-TB	24.0	29.95	29.9	1,000
14	B14B-PH-SM4-TB	S14B-PH-SM4-TB	26.0	31.95	31.9	1,000
15	B15B-PH-SM4-TB	S15B-PH-SM4-TB	28.0	33.95	33.9	1,000
16	B16B-PH-SM4-TB	—	30.0	35.95	-	1,000

Material and Finish

P1

COLOR

OPEN

1

YELLOW

2

BLACK

3

RED

④		HOUSING	JST B3B-PH-SM4-T COLOR:WHITE	1	PCS
③		TERMINAL	JST SPH-002T-P0. 5S	3	PCS
②		HOUSING	JST PHR-03V COLOR:WHITE 2. 0MM	1	PCS
①		CABLE	UL1007 28# (7/0. 12TC) OD:1. 2MM JACKET:PVC RED	1	PCS
			UL1007 28# (7/0. 12TC) OD:1. 2MM JACKET:PVC BLACK	1	PCS
			UL1007 28# (7/0. 12TC) OD:1. 2MM JACKET:PVC YELLOW	1	PCS
NO.	PART NO	ITEM	DESCRIPTION	Q' TY	UNIT

RoHS COMPLIANT

DRAWN BY

CHECKED BY

APPROVED BY

东莞市博帆科技有限公司

Dongguan Bofan Technology Co., Ltd.

TEL:076938835098/38835095 FAX:076938835091

比例: FREE

TITLE: JST-PHR-03V TO OPEN

單位: mm

SUPPLIER`S ITEM: BCCA3815

CUSTOMER:

CUSTOMER`S ITEM:

DRAWING NO. BCCA3815

DATE

2025.02.13