



Okystar Technology Co., Ltd.

Tel: 0086-755-23878860 Web: [www.okystar.com](http://www.okystar.com) [www.okynewstar.en.alibaba.com](http://www.okynewstar.en.alibaba.com)

Add: Room1105, Block B, ChinTo Technology Building, Minzhi Road, LongHua, Shenzhen, China

---



SKU:OKY3068-1

Name: DHT11 Digital Temperature And Relative Humidity Sensor Module  
PCB DIY Starter Kit

Specification:

1. Weight: 4g
2. Power supply voltage: 3.3~5.5V DC\
3. Output: the single bus digital signal
4. Measuring range: 20-90%RH humidity, temperature 0~50°
5. The measurement accuracy of +-5%RH: humidity, temperature +-2 °
6. Resolution: 1%RH humidity, temperature 1 °
7. Exchangeability: fully interchangeable
8. Long term stability: <  $\pm$  1%RH/
9. Response time: <5 seconds
10. Low power consumption



Okystar Technology Co., Ltd.

Tel: 0086-755-23878860 Web: [www.okystar.com](http://www.okystar.com) [www.okynewstar.en.alibaba.com](http://www.okynewstar.en.alibaba.com)

Add: Room1105, Block B, ChinTo Technology Building, Minzhi Road, LongHua, Shenzhen, China

---

Package List:

1 \* DHT11 Digital Temperature And Relative Humidity Sensor Module PCB

DIY Starter Kit