





Unit: mm

**PART SPECIFICATIONS (产品规格) :**

- | | |
|--|---|
| 1. Operating Voltage (工作电压) : 5VDC | 5. IP Rating (防尘防水等级): IP65 |
| 2. Supply Current (功率) : 10mA Max. @5.0VDC | 6. High-pot(耐压): 500V@ 1minutes |
| 3. PULSES: (脉冲) : 64 PPR | 7. Operating Tem. (使用温度) : -40°C~105°C |
| 4. Hardware (配件) : Nut&Washer (SUS303螺母&SUS304垫片) | 8. ROTATIONAL LIFE (寿命) : 3,000K CYCLES |
| 9. Rotation Torque (扭矩) : Light Feeling Detent , 40gf.cm Max. | |
| 10. Output Code (输出代码) : 2 Bit quadrature, channel A leads channle B during clockwise rotation of the shaft. | |

酷卡 (中山) 科技有限公司
COOKA (ZHONGSHAN) TECHNOLOGY LTD

CUSTOMER (客户) :
GENERAL

PART NAME (料号) :
ENS22S001

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS
ANGLES $\pm 3^\circ$
0PL 0.5; 1 PL ± 0.2 ; 2 PL ± 0.1

SIZE
A4

SCALE:

REV
A

1.0X

DRAWN BY:
Jason Smith

APPROVED BY:
Paul Jolley

CHECKED BY:
Peter Walker

ISSUED DATE :
2021-09-10

PART SERIES (产品系列) :
ENS22