

UG-2832HSWEG04 0.91" PM OLED OLED for Univision, replacement

UG-2832HSWEG04 0.91" PM OLED OLED for Univision

Panel Brand	Univision
Panel Model	UG-2832HSWEG04
Panel Type	PM-OLEDOLED
Panel Size	0.91"
Resolution	128×32
Display Mode	White Character
Surface	
Brightness	150 cd/m ² (Typ.)
Contrast Ratio	2000 : 1 (Min.) (Transmissive)
Display Colors	Monochrome (1-bit)
Response Time	
Viewing Angle	80/80/80/80 (Min.)(CR?10) (L/R/U/D)
Frequency	
Lamp Type	self
Signal Interface	4 Wire SPI
Input Voltage	2.8/7.25V (Typ.)(VDD/VCC)
Other Name	UG-2832HSWEGO4



