

Features

- Waterproof
- Washable
- Easy Sewing
- 360° Luminous
- Flexible and Foldable

Applications

- Sporting Goods
- Safety Application
- Internal Décor
- Wearable

MX01 SERIES LED FABRIC


Description

Flexible, easy to use linear LED fabric which can be applied to your clothing and accessories.

Key Specification

<i>.</i>				
LED life	20000 hours.			
LED color	White / Blue / Green / Red / Amber / Yellow /			
	Yellow Green / Turquoise / Rose Gold / Magenta			
Operating temperature	0°c~30°c			
Breaking strength	More than 30Kg			
Outside diameter:	3.0 ± 0.5mm			
Sewing space	7.0 ± 0.5mm			
Input voltage	DC 4.5 V			
Maximum current	< 250mA/m			
LED Pitch	20 ± 2mm; 40 ± 2mm			
Waterproof and Dustproof	IP68(IEC60598-1)			

Fabric Outline



Part Numbers

М	Х	01	RED -	P2		
Material	Dice	LED Package	Color	LED Pitch	Packing	Total Length
LED Fabric	X: No Dice	01: 0603 LED	White Blue Green Red Amber Yellow Yellow Green Turquoise Rose Gold Magenta	P2: 2cm P4: 4cm	(Blank): Bag package X: Paper Tube	(Blank): 1M 0X: 125M



Washing conditionsTested Procedure: AATCC135-2012Machine Cycle: NormalWashing Temp.: 27 +/- 3°CDrying Procedure: Line (Dryers Prohibited)Note: Use of laundry bag is recommended

Inolux Corporation Proprietary & Confidential