





iPixel LED Light Co. , Ltd



8*32 Flexible LED Panel Addressable WS2812B LED

Applications:

DIY electronic production
Advertising
Display



Features and Benefits:

- each LED built a Ws2811 IC chip inside,Addressable
- Pcontrol by SD controller,DMX512,Artnet
- Flexible PCB 5V low voltage input;
- PCB Color: Black
- Absolutely addressable ,each IC built inside RGB LED

Add: A2 Building Ming Jin hai Industrial Park,Zhou shi Rd ,Shiyan,Baoan,Shenzhen,China. 518108

Tel: 0086-755-85257292 Fax:0086-755-85259059 Web:www.ipixelleds.com

E-mail: inquiry@ipixelleds.com



iPixel LED Light Co. , Ltd





Technical Parameters:

Light source	SMD5050 RGB
Beam angle	140 deg.
Operating voltage	DC5V
Consumption watts	75(max) W
Pixel pitch (mm)	10mm
Pixel resolution (Dot/Panel)	256 Pixel
Entire piece LED quantity	256 pcs
Printed circuit board thickness	0.25mm
Operation Temperature	-40℃-40℃
Storage Temperature	-10℃-50℃

Technical Parameter

Part Number	Emitting Color	LED type	Voltage (V)	IC	Lumen per Panel	IP
S832WS2812	RGB	WS2812B	5	WS 2811	R:102400 G:179200 B:48640	Non-waterproof

Outline Dimension: (Unit:mm)



Add: A2 Building Ming Jin hai Industrial Park,Zhou shi Rd ,Shiyan,Baoan,Shenzhen,China. 518108

Tel: 0086-755-85257292 Fax:0086-755-85259059 Web:www.ipixelleds.com

E-mail: inquiry@ipixelleds.com