



Flexible Speaker 13cm x 18cm

Circuit Technology by Spectra Symbol



Complete with Amplifier

Features

- Thin
- Flexible
- Wearable
- Low Power

Standard Capabilities

Amp


Electrical

Input: 3.0 - 5.5 VDC
 Standby Current Draw: 33mA
 Normal Current Draw: 100mA
 Maximum Current Draw: 250mA
 Vo: 800Vpp (Max)
 HPF(-3dB)=500Hz
 LPF(-3dB)=6.6KHz

Dimensions

4.862cm x 2.286cm [1.9" x 0.9"]

Frequency Response



Speaker

Electrical

Power Consumption: Less than 0.2W (at 1kHz with 100Vrms input voltage)
 Maximum Input Voltage: 300 Vrms at 1kHz
 Polarity: Red cord is positive.

Dimensions

12.8cm x 18.3cm x 0.205cm [5.03" x 7.20" x 0.08"]

Audio Specifications

Effective Frequency Range: 650Hz~18kHz
 Mean SPL: >82 dB
 THD: <11% at 1.5kHz

Frequency Response

