

Complete with Amplifier

## Features

Thin  
Flexible  
Wearable  
Low Power

## Standard Capabilities

### Amp


#### Electrical

Input: 3.0 - 5.5 VDC  
Standby Current Draw: 33mA  
Normal Current Draw: 50mA  
Maximum Current Draw: 125mA  
Vo: 800Vpp (Max)  
HPF(-3dB)=500Hz  
LPF(-3dB)=6.6KHz

#### Dimensions

4.862cm x 2.286cm [1.9" x 0.9"]

#### Frequency Response



### Speaker

#### Electrical

Power Consumption: Less than 0.1W (at 2kHz with 100Vrms input voltage)  
Maximum Input Voltage: 300 Vrms at 1kHz  
Polarity: Red cord is positive.

#### Dimensions

12.8cm x 18.3cm x 0.205cm [5.03" x 7.20" x 0.08"]

#### Audio Specifications

Effective Frequency Range: 700Hz~25kHz  
Mean SPL: >72 dB  
THD: <11% at 2kHz

#### Frequency Response

