





SPECIFICATION

Current:3A
 Operating Temperature:-55°C~+105°C
 Contact Resistance:20Milliohms Max
 Insulation Resistance:1000Megohms Min
 Withstanding Voltage:AC 1000V Rms
 Housing:Thermoplastic UL94V-0
 Contact:Copper Alloys



Recommended PCB Layout



4UCON 元化興業股份有限公司
 4UCON TECHNOLOGY INC.

DRAWING No.
 18798

APPROVED BY MEI
 CHECKED BY HZF
 DRAWING BY JLT

UNLESS OTHERWISE SPECIFIED
 TOLERANCES ARE
 .X ±0.38
 .XX ±0.25
 ANG: ±5°

SCALE NONE

REV. A0

UNIT mm

NO.	REV.	REVISIONS	CHK	DATE
△ A0		NEW RELEASE	HZF	06/15/2007