




STAINLESS STEEL  
 SOCKET TO ACCOMODATE  
 .10 [2.54mm] HIGH X .16 [4.06mm]  
 DIA. STUD



\* WIRE DIAMETER AND TYPE  
 OPTIONAL PER CUSTOMERS  
 SPECIFICATIONS.

REV.	DESCRIPTION	APPROVAL DATE	APPROVED BY
D	REV PER ECO #6704	GSOX 10/23/02	10/30/02 TS
C	REV PER ECO #03598	RT 6/19/98	6/19/98 RT
B	REV PER ECO #03435	RT 3/19/98	3/19/98 RT
A	RELEASE PER ECO 2209	SJ 8/19/96	8/28/96 KG

TOLERANCES UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN INCHES DIMENSIONS IN [ ] METRIC	
FRACTIONAL	±1/64
DECIMAL	.00 ±.01 [.25mm] .000 ±.005 [.127mm]
ANGULAR	±.5°

APPROVALS	DATE
DRAWN <i>Famison</i>	8/19/96
CHECKED <i>[Signature]</i>	10/24/02
PROJ ENGR	
APPROVED <i>[Signature]</i>	10/28/02
PROJECT	FSCM

**Plastics ONE**  
 HOLDING THE FUTURE  
 6591 MERRIMAN ROAD, S.W., ROANOKE, VA, 24018  
 PHONE: 540-772-7850 FAX: 540-989-7519

TITLE: **SNAP, 222**

SCALE: 5X

SIZE	DWG	REV	SHT
B	2052-50	D	1 OF 1