

Shenzhen Kinmore Motor Co.,Ltd

KM20100507

KM-12FN20-100-06120

OUTLINE





1.STANDARD OPERATING CONDITIONS:

- 1.1 Operating Voltage: DC 2.0~6.0V
- 1.2 Operating Temperature: -10~+60° C
- 1.3 Operating Humidity: 5~95%RH
- 1.4 Direction of Rotation:

Counter-clockwise when viewing motor output side with positive voltage applied to positive(red)terminal.

2.MEASURING CONDITIONS:

- 2.1 Voltage: DC 6V
- 2.2 Environmental temperature: 5° C~35° C
- 2.3 Environmental humidity: 40%~85%RH
- 2.4 Motor Position: Motor to be held with shaft horizontally.

3.ELECTRICAL CHARACTERISTICS

(At initial stage after 30 seconds run-in)

- 3.1 Rated
- 3.1.1 Rated Voltage:DC 6V
- 3.1.2 Rated Load: 150g.cm
- 3.2 No Load
- 3.2.1 No Load Speed: $120 \pm 10\%$ rpm
- 3.2.2 No load Current: ≤30mA
- 3.3 On Load
- 3.3.1 Rated Current: ≤135mA
- 3.3.2 Rated Speed: 95 \pm 10%rpm
- 3.4 Start
- 3.4.1 Start Torque: ≥550 g.cm
- 3.4.2 Start Voltage:≤1.2V
- 3.5 Stall

Stall Current: \leq 420mA Insulation Resistance \geq 1M Ω with DC100V

4.MECHANICAL CHARACTERISTICS:

- 4.1 End Play: 0. 05~0. 45mm
- 4.2 Shaft radial runout:less than 0.02mm, 3.00mm away from the end
- 4.3 Weight:~10g
- 4.4 Noise: ≤50dB (Distance:10cm,Background noise≤26dB)
- 4.5 Axial thrust ≤3kgf
- 4.6 Perpendicularity 90±1°
- 4.7 Dimension drawing: See < OUTLINE >

5.LIFETIME TEST:

After operating continuously for 50 hours on the condition of 150g.cm with rated voltage, RPM :within \pm 30% of initial value, Current :within \pm 30% of initial value and the motor with no obvious anomaly.

Customer Approval:

Tested By:	朱卫孙	Checked By:	陈彦平	Approved By:	刘国友
------------	-----	-------------	-----	--------------	-----