

**产品规格书****Specification of Product**

产品名称: 6V 1kg模拟舵机

Product Name: 6V 1kg.cm Analog Servo

产品型号 Model No. FS0005

**1. 使用环境条件 Apply Environmental Condition**

No.	Item	Specification
1-1	存储温度 Storage Temperature Range	-30°C~80°C
1-2	运行温度 Operating Temperature Range	-15°C~70°C

**2. 测试环境 Standard Test Environment**

No.	Item	Specification
2-1	温度 Temperature range	25°C ±5°C
2-2	湿度 Humidity range	65%±10%

**3. 机械特性 Mechanical Specification**

No.	Item	Specification
3-1	尺寸 Size	A: 21.5mm B: 11.8mm C: 20.9mm
3-2	重量 Weight	5g ±0.2
3-3	齿轮类型 Gear type	Plastic Gear(Nylon & POM )
3-6	机构极限角度 Limit angle	NO limit
3-7	轴承 Bearing	NO Ball bearings
3-8	出力轴 Horn gear spline	20T
3-9	摆臂 Horn type	Plastic, POM
3-10	外壳 Case	Plastic
3-11	舵机线 Connector wire	150mm ±5 mm
3-12	马达 Motor	Metal brush motor
3-13	防水性能 Splash water resistance	NO

**4. 电气特性 Electrical Specification (Function of the Performance)**

No.	工作电压 Operating Voltage Range	4.8V	6V
4-1*	静态电流 Idle current(at stopped)	5mA	6mA
4-2*	空载速度 No load speed	0.14sec/60degree	0.12sec/60degree
4-3*	空载电流 Runnig current(at no load)	60 mA	70 mA
4-4	堵转扭矩 Peak stall torque	0.8kg.cm	1kg.cm
		11.13oz.in	13.91oz.in
4-5	堵转电流 Stall current	500 mA	600mA

Note: "\*"definition is average value when the servo runing with no load

产品名称: 6V 1kg模拟舵机  
 Product Name: 6V 1kg.cm Analog Servo

产品型号 Model No. FS0005

**5. 控制特性 Control Specification:**

No.	Item	Specification
5-1	控制信号 Command signal	Pulse width modification
5-2	放大器类型 Amplifier type	Analog comparator
5-3	脉冲宽度范围 Pulse width range	900~2100μsec
5-4	停止位置 Stop position	1500μsec
5-5	旋转角度 Running degree	120° (when 900~2100 μ sec)
5-6	死区宽度 Dead band width	4μsec
5-7	旋转方向 Rotating direction	Counter Clockwise (when 1000~2000 μsec)

**6. 外形图 The Drawings**
