

QRE1113, QRE1113GR Miniature Reflective Object Sensor


Features

- Phototransistor Output
- No Contact Surface Sensing
- Miniature Package
- Lead Form Style: Gull Wing


- Two Leadform Options: Through Hole (QRE1113)
 - SMT Gull Wing (QRE1113GR)
- Two Packaging Options: Tube (QRE1113)

Tape and Reel (QRE1113GR)


QRE1113GR Package Dimensions








LAND PATTERN RECOMMENDATION





- A. NO INDUSTRY STANDARD APPLIES
 TO THIS PACKAGE
 B. ALL DIMENSIONS ARE IN MILLIMETERS
 C. TOLERANCE OF ±0.15MM ON ALL
 NON-NOMINAL DIMENSIONS

- D. DRAWING FILENAME: MKT-ARU313Arev2

QRE1113 Package Dimensions(1, 2)








Notes:

- 1. Dimensions for all drawings are in millimeters.
- 2. Tolerance of ±0.15 mm on all non-nominal dimensions.

Schematic



Pin 1: Anode Pin 2: Cathode Pin 3: Collector Pin 4: Emitter

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at $T_A = 25^{\circ}\text{C}$ unless otherwise noted.

Symbol	Parameter	Value	Unit
T _{OPR}	Operating Temperature	-40 to +85	°C
T _{STG}	Storage Temperature	-40 to +90	°C
T _{SOL-I}	Soldering Temperature (Iron) ^(4 5, 6)	240 for 5 sec	°C
T _{SOL-F}	Soldering Temperature (Flow) ^(5, 6)	260 for 10 sec	°C
EMITTER			
I _F	Continuous Forward Current	50	mA
V _R	Reverse Voltage	5	V
I _{FP}	Peak Forward Current ⁽⁷⁾	1	А
P _D	Power Dissipation ⁽³⁾	75	mW
SENSOR			
V _{CEO}	Collector-Emitter Voltage	30	V
V _{ECO}	Emitter-Collector Voltage	5	V
I _C	Collector Current	20	mA
P _D	Power Dissipation ⁽³⁾	50	mW

Electrical / Optical Characteristics

Values are at $T_A = 25$ °C unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit			
INPUT DIODE									
V _F	Forward Voltage	I _F = 20 mA		1.2	1.6	V			
I _R	Reverse Leakage Current	V _R = 5 V			10	μΑ			
λ _{PE}	Peak Emission Wavelength	I _F = 20 mA		940		nm			
OUTPUT TRANSISTOR									
I _D	Collector-Emitter Dark Current	$I_F = 0 \text{ mA}, V_{CE} = 20 \text{ V}$			100	nA			
COUPLED									
I _{C(ON)}	On-State Collector Current	$I_F = 20 \text{ mA}, V_{CE} = 5 \text{ V}^{(8)}$	0.10	0.40		mA			
I _{CX}	Cross-Talk Collector Current	$I_F = 20 \text{ mA}, V_{CE} = 5 \text{ V}^{(9)}$			1	μΑ			
V _{CE(SAT)}	Saturation Voltage				0.3	V			
t _r	Rise Time	$V_{CC} = 5 \text{ V}, I_{C(ON)} = 100 \mu\text{A},$		20		μS			
t _f	Fall Time	$R_L = 100 \text{ k}\Omega$		20		μS			

Notes:

- 3. Derate power dissipation linearly 1.00 mW/°C above 25°C.
- 4. RMA flux is recommended.
- 5. Methanol or isopropyl alcohols are recommended as cleaning agents.
- 6. Soldering iron 1/16" (1.6mm) from housing.
- 7. Pulse conditions: $tp = 100 \mu s$; T = 10 ms.
- 8. Measured using an aluminum alloy mirror at d = 1 mm.
- 9. No reflective surface at close proximity.

Typical Performance Curves




Fig. 1 Normalized Collector Current vs. Distance between device and reflector




Fig. 2 Collector Current vs. Forward Current




Fig. 3 Normalized Collector Current vs. Collector to Emitter Voltage




Fig. 4 Collector Emitter Dark Current (Normalized) vs. Ambient Temperature

Typical Performance Curves (Continued)




Fig. 6 Forward Current vs. Forward Voltage




Fig. 7 Rise and Fall Time vs. Load Resistance




Fig. 8 Forward Voltage vs. Ambient Temperature





Fig. 8 Radiation Diagram


Taping Dimensions for GR option

Progressive Direction




General tolerance ±0.1 Dimensions in mm

Reel Dimensions



Reflow Profile



Note: Reflow soldering should not be done more than twice.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative