
# **GNSS Antennas**



GNSS Active Patch and Flexible antennas complement ceramic and LDS-MID chip selections for superior signal processing and ground-independence over a wide range of navigation and tracking applications

## **Features and Advantages**



\*The series 206640 antenna is an active patch antenna with ceramic patch, ground plane (PCB), 2-stage LNA and SAW (Surface Acoustic Wave) filter - all integrated within a compact 25 by 25 by 6.5mm module complete with a 60mm cabled (IPEX-1 connector) extension.

transmitted by the ceramic antenna on it

### **Applications**

antenna and board

### Automotive

Navigation devices

### **Commercial Vehicles**

High-speed rail

#### Industrial

Drones

Maritime Port Technology Systems
Surveying and Mapping Systems

Emergency Response Systems



Automotive



Drones



Maritime Port Technology Systems

# **GNSS Antennas**



# **Specifications**

### REFERENCE INFORMATION

Packaging: Tape-and-Reel (146216, 146235, 204283) Tray (146168, 204286, 206640, 208890) PET Film (206560)

Designed In: mm RoHS: Yes Halogen Free: Yes

#### **ELECTRICAL**

RF Power (Watt): 2 Average Total Radiation Efficiency: Refer to Product Specifications Peak Gain: Refer to Product Specifications

### **MECHANICAL**

Refer to Product Specifications

Input Impedance (ohms): 50

#### **PHYSICAL**

Housing: Ceramic (206640, 204286, 204283, 146168, 208890) Flexi (206560)

LDS-MID (146216, 146235) Plating: Refer to Sales Drawings Operating Temperature:

-40 to +85°C (206560, 206640) -40 to +125°C (146168, 146216, 146235, 204283, 204286) -30 to +85°C (208890)

# **GNSS Antenna Family**

Antennas	GNSS Flexible Antenna (206560)	GNSS Active Patch Antenna with Low-Noise Amplifier (206640)	Helix GPS Antenna (146235)	RHCP LDS-MID GPS Antenna (146216)	RHCP Ceramic GPS Antenna (146168)	GPS/BEIDOU/ GLONASS Ceramic Antenna (204286)	Low-profile GNSS Ceramic Antenna (204283)	Low-profile GPS Ceramic Antenna (208890)
Dimension	40.40 by 15.40mm	25.00 by 25.00 by 6.50mm	3.00 by 5.00 by 4.00mm	11.80 by 11.55 by 6.00mm	25.00 by 25.00 by 4.00mm	25.00 by 25.00 by 4.00mm	3.20 by 1.60 by 1.10mm	18.00 by 18.00 by 2.00mm
PCB Clearance	No clearance	No clearance	4mm x 6mm	No clearance	No clearance	No clearance	5mm x 6mm	No clearance
Material	Flexi	Ceramic + PCB + Tin Plate	LDS	LDS	Ceramic	Ceramic	Ceramic	Ceramic
Antenna Type	Dipole	Active Patch	Monopole	PIFA	Patch	Patch	Loop	Patch
Frequency Range	1561 – 1602 MHz	1561 – 1602 MHz	1561 – 1602 MHz	1575 MHz	1575 MHz	1561 – 1602 MHz	1561 – 1602 MHz	1575 MHz
Return Loss	< -8dB	- 8dB (VSWR 2.5)	<-8dB	<-10dB	<-15dB	<-10dB	<-10dB	<-15dB
Peak Gain	1.5dBi	LNA 28dB	1.1dBi	1dBi	5.5dBi	5.5dBi	2.0dBi	2.6dBi
Total Efficiency	> 74% (50mm)	NA	>50%	>55%	>75%	>70%	>60%	>45%
Polarization	Linear	RHCP	Elliptic	RHCP	RHCP	Elliptic	Linear	RHPC
Axial Ratio	N.A.	N.A.	<6.0	<3.0	<3.0	<13.0	N.A.	<2
					0		1	3

## **Ordering Information**

Series No.	Description	Mounting Style
206560	GNSS Flexible Antenna	Peel-and-stick
<u>206640</u>	GNSS Active Patch Antenna with Low-Noise Amplifier	SMT
204286	GPS/BEIDOU/ GLONASS Ceramic Antenna	Peel-and-stick
204283	Low-profile GNSS Ceramic Antenna	SMT
<u>146235</u>	Helix LDS-MID GPS Antenna	SMT
<u>146216</u>	RHCP LDS-MID GPS Antenna	SMT
<u>146168</u>	RHCP Ceramic GPS Antenna	Peel-and-stick
208890	18x18mm GPS Ceramic Antenna	Peel-and-stick

www.molex.com/link/gnss-gps.html