

RF-Hardened, Low-Noise Microphone with Bottom Port and Analog Output

GENERAL DESCRIPTION

The ICS-40180* is an analog MEMS microphone with high SNR and enhanced RF immunity. The ICS-40180 includes a MEMS microphone element, an impedance converter, and an output amplifier.

Other high-performance specification include a linear response up to 124 dB SPL, tight ±1 dB sensitivity tolerance, and enhanced immunity to both radiated and conducted RF interference.

The ICS-40180 is available in a small, $3.5 \text{ mm} \times 2.65 \text{ mm} \times$ 0.98 mm, surface-mount package.


APPLICATIONS

- **Smartphones**
- **Tablet Computers**
- Wearable Devices
- Still and Video Cameras
- **Bluetooth Headsets**
- Notebook PCs
- Security and Surveillance

FEATURES

- High 65 dBA SNR
- -38 dBV Sensitivity
- ±1 dB Sensitivity Tolerance
- Non-Inverted Signal Output
- Extended Frequency Response from 60 Hz to 20 kHz
- **Enhanced RF Immunity**
- 124 dB SPL Acoustic Overload Point
- Low Current Consumption: 190 µA
- Single-Ended Analog Output
- High -78 dBV PSR
- 3.5 × 2.65 × 0.98 mm Surface-Mount Package
- Compatible with Sn/Pb and Pb-Free Solder Processes
- **RoHS/WEEE Compliant**

FUNCTIONAL BLOCK DIAGRAM



ORDERING INFORMATION

PART	TEMP RANGE	PACKAGING	
ICS-40180	-40°C to +85°C	13" Tape and Reel	
EV_ICS-40180-FX	_		

Document Number: DS-000021 Revision: 1.2 Rev Date: 04/03/2015

^{*}Protected by U.S. Patents 7,449,356; 7,825,484; 7,885,423; and 7,961,897. Other patents are pending.



TABLE OF CONTENTS

General Description	1
Applications	1
Features	1
Functional Block Diagram	1
Ordering Information	1
Table of Contents	2
Specifications	3
Table 1. Electrical Characteristics	3
Absolute Maximum Ratings	4
Table 2. Absolute Maximum Ratings	4
ESD Caution	4
Soldering Profile	5
Table 3. Recommended Soldering Profile*	5
Pin Configuration And Function Descriptions	6
Table 4. Pin Function Descriptions	6
Typical Performance Characteristics	7
Applications Information	8
Codec Connection	8
Supporting Documents	9
Evaluation Board User Guide	9
Application Notes	9
PCB Design And Land Pattern Layout	10
PCB Material And Thickness	10
Handling Instructions	11
Pick And Place Equipment	11
Reflow Solder	11
Board Wash	11
Outline Dimensions	12
Ordering Guide	12
Revision History	13
Compliance Declaration Disclaimer	14



SPECIFICATIONS

TABLE 1. ELECTRICAL CHARACTERISTICS

 $T_A = 25$ °C, $V_{DD} = 1.5$ to 3.63 V, unless otherwise noted. Typical specifications are not guaranteed.

PARAMETER CONDITIONS		MIN	TYP	MAX	UNITS	NOTES
PERFORMANCE						
Directionality		Omni				
Output Polarity		Non-Inverted				
Sensitivity	1 kHz, 94 dB SPL	-39	-38	-37	dBV	
Signal-to-Noise Ratio (SNR)	20 Hz to 20 kHz, A-weighted		65		dBA	
Equivalent Input Noise (EIN)	20 Hz to 20 kHz, A-weighted		29		dBA SPL	
Dynamic Range	Derived from EIN and maximum		95		dB	
Dynamic Kange	acoustic input	95			ив	
Frequency Response	Low frequency –3 dB point		60		Hz	1
Frequency Response	High frequency −3 dB point		>20		kHz	1
Total Harmonic Distortion (THD)	105 dB SPL		0.3	1	%	
Power-Supply Rejection (PSR)	217 Hz, 100 mVp-p square wave	-78			dBV	
Power-supply Rejection (PSR)	superimposed on V _{DD} = 1.8 V			ubv	иву	
Power Supply Rejection Ratio (PSRR)	1 kHz, 100 mVp-p sine wave		-46		dB	
rower supply Rejection Ratio (FSRR)	superimposed on V _{DD} = 1.8 V		-40		uв	
Acoustic Overload Point	10% THD		124		dB SPL	
POWER SUPPLY					_	
Supply Voltage (V _{DD})		1.5		3.63	V	
Supply Current (I _S)	V _{DD} = 1.8 V		190	240	μΑ	
Supply Current (Is)	V _{DD} = 3.3 V		210	260	μΑ	
OUTPUT CHARACTERISTICS						
Output Impedance			350		Ω	
Output DC Offset			0.7		V	
Maximum Output Voltage	124 dB SPL input 0.398			V rms		
Noise Floor	20 Hz to 20 kHz, A-weighted, rms		-103		dBV	

Note 1: See Figure 3 and Figure 4.



ABSOLUTE MAXIMUM RATINGS

Stress above those listed as Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these conditions is not implied. Exposure to the absolute maximum ratings conditions for extended periods may affect device reliability.

TABLE 2. ABSOLUTE MAXIMUM RATINGS

PARAMETER	RATING
Supply Voltage (V _{DD})	-0.3 V to +3.63 V
Sound Pressure Level	160 dB
Mechanical Shock	10,000 g
Vibration	Per MIL-STD-883 Method 2007, Test Condition B
Temperature Range	
Biased	-40°C to +85°C
Storage	-55°C to +150°C

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore proper ESD precautions should be taken to avoid performance degradation or loss of functionality.



SOLDERING PROFILE




Figure 1. Recommended Soldering Profile Limits

TABLE 3. RECOMMENDED SOLDERING PROFILE*

PROFILE FEATURE		Sn63/Pb37	Pb-Free
Average Ramp Rate (T _L to T _P)		1.25°C/sec max	1.25°C/sec max
	Minimum Temperature (T _{SMIN})	100°C	100°C
Preheat	Minimum Temperature (T _{SMIN})	150°C	200°C
	Time (T_{SMIN} to T_{SMAX}), t_S	60 sec to 75 sec	60 sec to 75 sec
Ramp-Up Rate (T _{SMAX} to T _L)		1.25°C/sec	1.25°C/sec
Time Maintained Above Liquidous (t _L)		45 sec to 75 sec	~50 sec
Liquidous Temperature (T _L)		183°C	217°C
Peak Temperature (T _P)		215°C +3°C/-3°C	260°C +0°C/-5°C
Time Within +5°C of Actual Peak Temperature (t _P)		20 sec to 30 sec	
Ramp-Down Rate		Down Rate 3°C/sec max	
Time +25°C (t _{25°C}) to Peak Temperature		ature 5 min max 5 min ma	

^{*}The reflow profile in Table 3 is recommended for board manufacturing with InvenSense MEMS microphones. All microphones are also compatible with the J-STD-020 profile



PIN CONFIGURATION AND FUNCTION DESCRIPTIONS




Figure 2. Pin Configuration Top View (Terminal Side Down) Not to Scale

TABLE 4. PIN FUNCTION DESCRIPTIONS

PIN	NAME	FUNCTION
1	OUTPUT	Analog Output Signal
2	GND	Ground
3	GND	Ground
4	GND	Ground
5	VDD	Power Supply



TYPICAL PERFORMANCE CHARACTERISTICS




Figure 3. Frequency Response Mask




Figure 5. PSR vs. Frequency, 100 mV p-p Swept Sine Wave




Figure 7. Linearity




Figure 4. Typical Frequency Response (Measured)




Figure 6. Total Harmonic Distortion + Noise (THD+N) vs. Input SPL




Figure 8. Clipping Characteristics



APPLICATIONS INFORMATION

CODEC CONNECTION

The ICS-40180 output can be connected to a dedicated codec microphone input (see Figure 9) or to a high input impedance gain stage. A $0.1~\mu\text{F}$ ceramic capacitor placed close to the ICS-40180 supply pin is used for testing and is recommended to adequately decouple the microphone from noise on the power supply. A DC blocking capacitor is required at the output of the microphone. This capacitor creates a high-pass filter with a corner frequency at

$$f_C = 1/(2\pi \times C \times R)$$

where *R* is the input impedance of the codec.

A minimum value of 2.2 μ F is recommended in Figure 9 because the input impedance of some codecs can be as low as 2 $k\Omega$ at their highest PGA gain setting, which results in a high-pass filter corner frequency at 37 Hz. Figure 10 shows the ICS-40180 connected to an op amp configured as a noninverting preamplifier.




Figure 9. ICS-40180 Connected to a Codec




Figure 10. ICS-40180 Connected to an Op Amp



SUPPORTING DOCUMENTS

For additional information, see the following documents.

EVALUATION BOARD USER GUIDE

UG-325, Analog Output MEMS Microphone Flex Evaluation Board

APPLICATION NOTES

AN-100, MEMS Microphone Handling and Assembly Guide

AN-1003, Recommendations for Mounting and Connecting the InvenSense Bottom-Ported MEMS Microphones

AN-1112, Microphone Specifications Explained

AN-1124, Recommendations for Sealing InvenSense Bottom-Port MEMS Microphones from Dust and Liquid Ingress

AN-1140, Microphone Array Beamforming

AN-1165, Op Amps for Microphone Preamp Circuits

AN-1181, Using a MEMS Microphone in a 2-Wire Microphone Circuit



PCB DESIGN AND LAND PATTERN LAYOUT

Below is the lay out the PCB land pattern for the ICS-40180, at a 1:1 ratio to the solder pads on the microphone package, (see Figure 11.) Take care to avoid applying solder paste to the sound hole in the PCB. Figure 12 shows a suggested solder-paste stencil pattern layout. The response of the ICS-40180 is not affected by the PCB hole size, as long as the hole is not smaller than the sound port of the microphone (0.25 mm, or 0.01 inch, in diameter). A 0.5 mm to 1 mm (0.020 inch to 0.040 inch) diameter for the hole is recommended.

Align the hole in the microphone package with the hole in the PCB. The exact degree of the alignment does not affect the performance of the microphone as long as the holes are not partially or completely blocked.




Figure 11. Recommended PCB Land Pattern Layout




Figure 12. Recommended Solder Paste Stencil Pattern Layout

PCB MATERIAL AND THICKNESS

The performance of the ICS-40180 is not affected by PCB thickness. The ICS-40180 can be mounted on either a rigid or flexible PCB. A flexible PCB with the microphone can be attached directly to the device housing with an adhesive layer. This mounting method offers a reliable seal around the sound port while providing the shortest acoustic path for good sound quality.



HANDLING INSTRUCTIONS

PICK AND PLACE EQUIPMENT

The MEMS microphone can be handled using standard pick-and-place and chip shooting equipment. Take care to avoid damage to the MEMS microphone structure as follows:

- Use a standard pickup tool to handle the microphone. Because the microphone hole is on the bottom of the package, the pickup tool can make contact with any part of the lid surface.
- Do not pick up the microphone with a vacuum tool that makes contact with the bottom side of the microphone. Do not pull air out of or blow air into the microphone port.
- Do not use excessive force to place the microphone on the PCB.

REFLOW SOLDER


For best results, the soldering profile must be in accordance with the recommendations of the manufacturer of the solder paste used to attach the MEMS microphone to the PCB. It is recommended that the solder reflow profile not exceed the limit conditions specified in Figure 1 and Table 3.


BOARD WASH

When washing the PCB, ensure that water does not make contact with the microphone port. Do not use blow-off procedures or ultrasonic cleaning.



OUTLINE DIMENSIONS





DETAIL A

DIMENSION	MINIMUM	NOMINAL	MAXIMUM	
Α	0.880	0.980	1.080	
A1	0.190	0.230	0.270	
A2	0.710	0.750	0.790	
NUMBER OF LANDS 5				

Figure 13. 5-Terminal Chip Array Small Outline No-Lead Cavity [LGA_CAV] $3.5 \times 2.65 \times 0.98$ mm Body

Dimensions shown in millimeters




Figure 14. Package Marking Specification (Top View)

ORDERING GUIDE

PART	TEMP RANGE	PACKAGE	QUANTITY	PACKAGING
ICS-40180	-40°C to +85°C	5-Terminal LGA_CAV	10,000	13" Tape and Reel
EV_ICS-40180-FX	_	Flexible Evaluation Board	_	



REVISION HISTORY

REVISION DATE	REVISION	DESCRIPTION
10/7/2014	1.0	Initial Release
11/17/2014	1.1	Updated General Description information
04/03/2015	1.2	Corrected PSRR spec and replaced Figure 5



COMPLIANCE DECLARATION DISCLAIMER

InvenSense believes the environmental and other compliance information given in this document to be correct but cannot guarantee accuracy or completeness. Conformity documents substantiating the specifications and component characteristics are on file. InvenSense subcontracts manufacturing, and the information contained herein is based on data received from vendors and suppliers, which has not been validated by InvenSense.

This information furnished by InvenSense is believed to be accurate and reliable. However, no responsibility is assumed by InvenSense for its use, or for any infringements of patents or other rights of third parties that may result from its use. Specifications are subject to change without notice. InvenSense reserves the right to make changes to this product, including its circuits and software, in order to improve its design and/or performance, without prior notice. InvenSense makes no warranties, neither expressed nor implied, regarding the information and specifications contained in this document. InvenSense assumes no responsibility for any claims or damages arising from information contained in this document, or from the use of products and services detailed therein. This includes, but is not limited to, claims or damages based on the infringement of patents, copyrights, mask work and/or other intellectual property rights.

Certain intellectual property owned by InvenSense and described in this document is patent protected. No license is granted by implication or otherwise under any patent or patent rights of InvenSense. This publication supersedes and replaces all information previously supplied. Trademarks that are registered trademarks are the property of their respective companies. InvenSense sensors should not be used or sold in the development, storage, production or utilization of any conventional or mass-destructive weapons or for any other weapons or life threatening applications, as well as in any other life critical applications such as medical equipment, transportation, aerospace and nuclear instruments, undersea equipment, power plant equipment, disaster prevention and crime prevention equipment.

©2015 InvenSense, Inc. All rights reserved. InvenSense, MotionTracking, MotionProcessing, MotionProcessor, MotionFusion, MotionApps, DMP, AAR and the InvenSense logo are trademarks of InvenSense, Inc. Other company and product names may be trademarks of the respective companies with which they are associated.



©2015 InvenSense, Inc. All rights reserved.