

# MAX-M10 series



## u-blox M10 standard precision GNSS modules

### Ultra-low-power GNSS receiver for high-performance asset-tracking devices

- Less than 25 mW power consumption without compromising GNSS performance
- Maximum position availability with concurrent reception of 4 GNSS
- Proven excellent performance, even with small antennas
- Advanced spoofing and jamming detection
- Pin-compatible with previous MAX products



9.7 × 10.1 × 2.5 mm



### Product description

The MAX-M10 series is built on the ultra-low-power u-blox M10 GNSS platform, which provides exceptional sensitivity and acquisition times for all L1 GNSS systems.

The extremely low power consumption of less than 25 mW in continuous tracking mode allows great power autonomy for all battery-operated devices, such as asset trackers, without compromising on GNSS performance.

MAX-M10 supports concurrent reception of four GNSS (GPS, GLONASS, Galileo, and BeiDou). The high number of visible satellites enables the receiver to select the best signals. This maximizes the position availability, in particular under challenging conditions such as in deep urban canyons.

u-blox Super-S technology offers great RF sensitivity and can improve the dynamic position accuracy by up to 25% with small antennas or in a non-line-of-sight scenario.

The MAX-M10S module integrates an LNA followed by an SAW filter in the RF path for maximum sensitivity in passive antenna designs. MAX-M10M offers a cost and power optimized setup without LNA and SAW filter.

MAX-M10 detects jamming and spoofing attempts and reports them to the host, so that the system can react to such events. Advanced filtering algorithms mitigate the impact of RF interference and jamming, thus enabling the product to operate as intended.

Both modules offer backwards pin-to-pin compatibility with previous u-blox generations, which saves designers time and cost when upgrading their designs.

	MAX-M10M	MAX-M10S
<b>Grade</b>		
Automotive		
Professional	•	•
Standard		
<b>GNSS</b>		
GPS + QZSS/SBAS	•	•
GLONASS	•	•
Galileo	•	•
BeiDou	•	•
Number of concurrent GNSS	4	4
<b>Interfaces</b>		
UART	1	1
SPI		
DDC (I2C compliant)	1	1
<b>Features</b>		
Additional SAW		•
Additional LNA		•
RTC crystal	•	•
Oscillator	C	T
Timepulse	1	1
<b>Power supply</b>		
1.8 V – 5.5 V	•	
2.7 V – 3.6 V		•

C = Crystal / T = TCXO



## Product performance

Receiver type	u-blox M10 engine GPS L1 C/A, QZSS L1 C/A/S, GLONASS L10F BeiDou B1I/B1C, Galileo E1B/C SBAS L1 C/A: WAAS, EGNOS, MSAS, GAGAN		
Nav. update rate	Up to 10 Hz (4 concurrent GNSS)		
Horizontal position accuracy	1.5 m CEP		
		<b>MAX-M10M</b>	<b>MAX-M10S</b>
Acquisition <sup>1</sup>	Cold start	26 s	24 s
	Aided start	3 s	2 s
	Hot start	1 s	1 s
Sensitivity <sup>1</sup>	Tracking & Nav.	-164 dBm	-167 dBm
	Reacquisition	-161 dBm	-161 dBm
	Cold start	-148 dBm	-148 dBm
	Hot start	-159 dBm	-159 dBm

## Tracking features

u-blox Super-S	Improved accuracy with small antennas
Data batching	Autonomous tracking up to 10 min at 1 Hz
Odometer	Measure traveled distance with support for different user profiles

## Security features

Signal integrity	RF interference & jamming detection and reporting Active GNSS in-band filtering Spoofing detection and reporting
Device integrity	Receiver configuration lock by command
Secure interface	Signed UBX messages (SHA-256) JTAG debug interface disabled by default

## Electrical data

	<b>MAX-M10M</b>	<b>MAX-M10S</b>
Power supply	1.8 V to 5.5 V	2.7 V to 3.6 V
Power consumption at 3 V	2 GNSS: 19 mW	2 GNSS: 24 mW
	3 GNSS: 23 mW <sup>1</sup>	3 GNSS: 28 mW <sup>1</sup>
	4 GNSS: 27 mW	4 GNSS: 32 mW
Backup supply	1.65 V to 3.6 V	1.65 V to 3.6 V

<sup>1</sup> = For continuous tracking in default mode: GPS/BeiDou/Galileo + SBAS/QZSS

## NOTE:

This document provides an objective specification overview of this product. Please refer to the data sheet for details on firmware-related performance and feature support.

## Further information

For contact information, see [www.u-blox.com/contact-u-blox](http://www.u-blox.com/contact-u-blox).

For more product details and ordering information, see the product data sheet.

## Package

18 pin LCC (Leadless Chip Carrier): 9.7 × 10.1 × 2.5 mm, 0.6 g

## Environmental data, quality & reliability

Operating temp.	-40 °C to +85 °C
Storage temp.	-40 °C to +85 °C
Environmental grade	2015/863/EU RoHS-3
EMC (electromagnetic compatibility)	2014/53/EU RED
Environmental testing	ISO 16750
Quality management	Manufactured and fully tested in IATF 16949 certified production sites

## Interfaces

Serial interfaces	1 UART 1 DDC (I2C compliant)
Digital I/O	Configurable timepulse 1 EXTINT input for Wakeup
Raw Data output	Code phase data
Timepulse	Configurable: 0.25 Hz to 10 MHz
Supported antennas	Active and passive
Protocols	NMEA 4.10, UBX binary

## Services

Assisted GNSS	AssistNow GNSS Online: Data valid 2-4 hours AssistNow GNSS Offline: Data valid up to 35 days AssistNow Autonomous: Data valid up to 6 days OMA SUPL & 3GPP compliant
---------------	---

## Support products

EVK-M101	u-blox M10 GNSS evaluation kit with UBX-M10050-KB chip and I/O interface
u-center	Highly interactive and easy-to-use GNSS evaluation software

## Product variants

MAX-M10M	u-blox M10 concurrent GNSS LCC module, firmware in ROM, crystal oscillator
MAX-M10S	u-blox M10 concurrent GNSS LCC module, firmware in ROM, SAW filter, LNA, TCXO

## Legal Notice:

u-blox reserves all rights to this document and the information contained herein. Products, names, logos and designs described herein may in whole or in part be subject to intellectual property rights. Reproduction, use, modification or disclosure to third parties of this document or any part thereof without the express permission of u-blox is strictly prohibited.

The information contained herein is provided "as is". No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose or content of this document. This document may be revised by u-blox at any time. For most recent documents, please visit [www.u-blox.com](http://www.u-blox.com).