





2.95

1.0mm pitch/Disconnectable Crimp style connectors

Specifications -

• Voltage rating: 50 V AC, DC • Temperature range: -25°C to +85°C

• Current rating: 1.0 A AC, DC (AWG #28)

• Contact resistance: Initial value/ 20 mΩ max.

Applicable wire: Conductor size/ AWG #32 to #28

* Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.


 Insulation resistance: 100 MΩ min. Withstanding voltage: 500 VAC/minute

(including temperature rise in applying

After environmental tests/ 40 m Ω max.

electrical current)


Insulation O.D./ 0.4 to 0.8 mm



The world's first 1.0mm pitch crimp style connector.

- Compact, low profile design
- Compatible with the SR insulation displacement connectors
- Housing lances

PC board layout and Assembly layout



Side entry type


* Contact JST for details.

* Compliant with RoHS.

Standards -

Recognized E60389


Certified LR20812



Note: 1. The above figure is the figure viewed from the connector mounting side. 2. Tolerances are non-cumulative: ±0.05 mm for all centers.

3. The dimensions above should serve as a guideline. Contact JST for details.

Contact



Madal Na		Q'ty/				
Model No.	mm ²	AWG#	Insulation O.D. (mm)	reel		
SSH-003T-P0.2-H	0.032~0.08	32~28	0.4~0.8	23,000		
Metavial and Finish						

Phosphor bronze,	tin-plated	(reflow treatment)

RoHS compliance

Note: Contact JST for gold-plated products.


.	Crimping	Applicator				
Contact	machine	Crimp applicator	Dies	Crimp applicator with dies		
COLL COST DO O LL	AP-K2N	MKS-L-10-3	MK/SSH/L-003-02	APLMK SSH/L003-02		
55H-0031-P0.2-H		*MKS-SC	SC/SSH/L-003-02	APLSC SSH/L003-02		

Note: *Strip-crimp applicator

Contact JST for applicable wires in case that it is not usable due to wire size.

SH CONNECTOR

Housing




IVIOUE				Dimensions (mm)			
	Model No.		E	Q'ty/			
With protrusions Without protrusions		A	With protrusions	Without protrusions	box		
-02V-S-B	SHR-02V-S	1.0	5.0	3.0	2,00		
-03V-S-B	SHR-03V-S	2.0	6.0	4.0	2,00		
-04V-S-B	SHR-04V-S	3.0	7.0	5.0	2,00		
-05V-S-B	SHR-05V-S	4.0	8.0	6.0	2,00		
-06V-S-B	SHR-06V-S	5.0	9.0	7.0	2,00		
-07V-S-B	SHR-07V-S	6.0	10.0	8.0	2,00		
-08V-S-B	SHR-08V-S	7.0	11.0	9.0	2,00		
-09V-S-B	SHR-09V-S	8.0	12.0	10.0	2,00		
-10V-S-B	SHR-10V-S	9.0	13.0	11.0	2,00		
-11V-S-B	SHR-11V-S	10.0	14.0	12.0	2,00		
-12V-S-B	SHR-12V-S	11.0	15.0	13.0	2,00		
-13V-S-B	SHR-13V-S	12.0	16.0	14.0	2,00		
-14V-S-B	SHR-14V-S	13.0	17.0	15.0	2,00		
-15V-S-B	SHR-15V-S	14.0	18.0	16.0	2,00		
-20V-S-B	_	19.0	23.0	21.0	1,00		
	-	W-S-B —	W-S-B — 19.0	V-S-B — 19.0 23.0			

PBT, UL94V-0, natural (white)

RoHS compliance

Shrouded header

The shrouded headers are interchangeable with those of the SR insulation displacement connectors.



0	Model No.		Dimensions (mm)		Q'ty/reel		
Circuits	Top entry type	Side entry type	А	В	Top entry type	Side entry type	
2	BM02B-SRSS-TB	SM02B-SRSS-TB	1.0	4.0	1,500	3,000	
3	BM03B-SRSS-TB	SM03B-SRSS-TB	2.0	5.0	1,500	3,000	
4	BM04B-SRSS-TB	SM04B-SRSS-TB	3.0	6.0	1,500	3,000	
5	BM05B-SRSS-TB	SM05B-SRSS-TB	4.0	7.0	1,500	3,000	
6	BM06B-SRSS-TB	SM06B-SRSS-TB	5.0	8.0	1,500	3,000	
7	BM07B-SRSS-TB	SM07B-SRSS-TB	6.0	9.0	1,500	3,000	
8	BM08B-SRSS-TB	SM08B-SRSS-TB	7.0	10.0	1,500	3,000	
9	BM09B-SRSS-TB	SM09B-SRSS-TB	8.0	11.0	1,500	3,000	
10	BM10B-SRSS-TB	SM10B-SRSS-TB	9.0	12.0	1,500	3,000	
11	BM11B-SRSS-TB	SM11B-SRSS-TB	10.0	13.0	1,500	3,000	
12	BM12B-SRSS-TB	SM12B-SRSS-TB	11.0	14.0	1,500	3,000	
13	BM13B-SRSS-TB	SM13B-SRSS-TB	12.0	15.0	1,500	3,000	
14	BM14B-SRSS-TB	SM14B-SRSS-TB	13.0	16.0	1,500	3,000	
15	BM15B-SRSS-TB	SM15B-SRSS-TB	14.0	17.0	1,500	3,000	
20	—	SM20B-SRSS-TB	19.0	22.0	—	3,000	
	Material and Finish						

Contact: Copper alloy, copper-undercoated, tin-plated (reflow treatment) Housing: PA, UL94V-0, natural (ivory) Solder tab: Brass, copper-undercoated, tin-plated (reflow treatment)

RoHS compliance This product displays (LF)(SN) on a label.

Note: 1. The products listed above are supplied on embossed-tape.

2. Contact JST for the headers with gold-plated pins.

3. Contact JST for the top entry type headers with suction cap.