


DATASHEET

0.8mm Height Flat Top Infrared LED

SIR19-21C/TR8



Features

- Small double-end package
- Low forward voltage
- Good spectral matching to Si photo detector
- Package in 8mm tape on 7" diameter reel
- Pb free
- The product itself will remain within RoHS compliant version.

Descriptions

- SIR19-21C/TR8 is an infrared emitting diode in miniature SMD package which is molded in a water clear plastic with flat top view lens.
- The device is spectrally matched with silicon photodiode and phototransistor.

Applications

- PCB mounted infrared sensor
- Infrared remote control units with high power requirement
- Scanner
- Infrared applied system

Device Selection Guide

Part Category	Chip Material	Lens Color	
SIR	GaAlAs	Water clear	

1

www.everlight.com


Copyright © 2013, Everlight All Rights Reserved. Release Date :2013/6/3. Issue No:DIR-0000964. Rev:3

Revision : 3 LifecyclePhase: Approved

Expired Period: Forever

Release Date:2013-06-21 04:30:09.0

Package Dimensions



Notes: 1. All dimensions are in millimeters

2.Tolerances unless dimensions ±0.1mm

Revision

Release Date:2013-06-21 04:30:09.0

Absolute Maximum Ratings (Ta=25)

Parameter	Symbol	Rating	Units
Continuous Forward Current	I_{F}	65	mA
Reverse Voltage	V_R	5	V
Operating Temperature	T_{opr}	-25 ~ +85	
Storage Temperature	T_{stg}	-40 ~ +85	
Soldering Temperature *1	T_{sol}	260	
Power Dissipation at(or below) 25 Free Air Temperature	P _d	110	mW

Notes: *1 Soldering time 5 seconds.

Electro-Optical Characteristics (Ta=25)

_		`	,			
Parameter	Symbol	Condition	Min.	Typ.	Max.	Units
Radiant Intensity	Ie	$I_F=20mA$	0.2	0.5		mW/sr
Peak Wavelength	p	$I_F=20mA$		875		nm
Spectral Bandwidth		I _F =20mA		80		nm
Forward Voltage	V_{F}	$I_F=20mA$	\	1.3	1.6	V
Reverse Current	I_R	$V_R=5V$		1	10	μA
View Angle	2 1/2	I _F =20mA		145		deg

3

Revision

: 3

www.everlight.com

Release Date:2013-06-21 04:30:09.0

Copyright © 2013, Everlight All Rights Reserved. Release Date :2013/6/3. Issue No:DIR-0000964. Rev:3

LifecyclePhase: Expired Period: Forever

EVERLIGHT

Typical Electro-Optical Characteristics Curves

Fig.1 Forward Current vs.

Ambient Temperature




Fig.2 Spectral Distribution




Fig.3 Relative Intensity vs Forward Current





Fig.4 Forward Current vs Forward Voltage



Copyright © 2013, Everlight All Rights Reserved. Release Date :2013/6/3. Issue No:DIR-0000964. Re

www.everlight.com


Revision : 3 Release Date:2013-06-21 04:30:09.0

LifecyclePhase: Approved Expired Period: Forever



Typical Electro-Optical Characteristics Curves

. Fig.5 Relative Radiant Intensity vs
Angular Displacement



Revision

LifecyclePhase: 正式發行

: 3

Release Date:2013-06-21 04:30:09.0


Expired Period: Forever

Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package, the LEDs should be kept at 30 or less and 90%RH or less.
 - 2.3 The LEDs should be used within a year.
 - 2.4 After opening the package, the LEDs should be kept at 30 or less and 70% RH or less.
 - 2.5 The LEDs should be used within 168 hours (7 days) after opening the package.
 - 2.6 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. for 24 hours.
- Baking treatment: 60±5
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

6

www.everlight.com

Release Date: 2013-06-21 04:30:09.0

Expired Period: Forever LifecyclePhase:

Copyright © 2013, Everlight All Rights Reserved. Release Date :2013/6/3. Issue No:DIR-0000964.




4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350 for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



7

Revision

: 3

Copyright © 2013, Everlight All Rights Reserved. Release Date :2013/6/3. Issue No:DIR-0000964. Rev:3


www.everlight.com

Release Date:2013-06-21 04:30:09.0

LifecyclePhase: Expired Period: Forever




Package Dimensions



Note: The tolerances unless mentioned are ±0.1, unit=mm.

Carrier Taping Dimensions: Loaded Quantity 3000PCS/Reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

8

Copyright © 2013, Everlight All Rights Reserved. Release Date :2013/6/3. Issue No:DIR-0000964. Rev:3

www.everlight.com

Revision : 3 LifecyclePhase: Approved Release Date:2013-06-21 04:30:09.0

Expired Period: Forever

EVERLIGHT

Label Form Specification



CPN: Customer's Production Number

P/N : Production Number QTY: Packing Quantity

CAT: Ranks

HUE: Peak Wavelength

REF: Reference

LOT No: Lot Number

Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD.

Office: No. 6-8, Zhonghua Rd., Shulin Dist.,

New Taipei City 23860, Taiwan

Tel: 886-2-2685-6688

Fax: 886-2685-2699, 6897

http://www.everlight.com

9

Revision

: 3

Copyright © 2013, Everlight All Rights Reserved. Release Date :2013/6/3. Issue No:DIR-0000964. Rev:3

www.everlight.com

LifecyclePhase: 正式發行 Approved Exp

Release Date:2013-06-21 04:30:09.0

Expired Period: Forever