
iPixel LE 



ipixe . ED



**3W LED Star** 




TOP VIEW

7.26

1.15

ipixelLE


D




LED

LED

BOTTOM VIEW






03.0 1.5 1.6

 $\geq$ 

Slug o DK



## iPixel LED Pixel LED

iPixelLED

Part Number	Emitting Color	Forward Current ( (mA)	Power	nm (K)	Voltage	Luminous
SJ-3W-R	RED	750	3	620630	2-2.8	75105
SJ-3W-Y	YELLOW	750	3	585595	2-2.8	75105
SJ-3W-B	BLUE	750	3	460470	3.2-3.8	3060
SJ-3W-G	GREEN	750	3	520530	3.2-3.8	75105
SJ-3W-CW	WHITE	750	3	60007000	3.2-3.8	160240
SJ-3W-WW	WARM WHITE	750	3	80003300	3.2-3.8	160200

ipixelLED

	Absolute Maxir	mum Ratings At Ta=2	50	ED	
0	Parameter	oixel	Red/Yellow	Blue/Green/White	oixel
	Viewing Angle	11	125±5	125±5	N.
ļ	Peak Pulsed Forward Current (mA) 1/10s		3000	1500	
ļ	Reverse Voltage(V	v)	≥8	≥5	LED
8	Reverse Current(uA)		≤30	≤50	ipixer
	ESD Sensitivity(V)		2000	2000	
Storage Temperature( $^{\circ}$ C)		ature(℃)	-40 to +100	-40 to +100	
ļ	Operating Temperature ( $^{\circ}$ C)		-30 to +55	-30 to +100	eller
8	Lead Soldering Te	:mperature(°C)	260 for 5 seconds Max	260 for 5 seconds Max	ipix

ipixelLED