



## **MODEL B+**

Product Name Raspberry Pi Model B+

**Product Description** The Raspberry Pi Model B+ incorporates a number of enhancements

and new features. Improved power consumption, increased connectivity and greater IO are among the improvements to this

powerful, small and lightweight ARM based computer.

**Specifications** 

Chip Broadcom BCM2835 SoC

Core architecture ARM11

CPU 700 MHz Low Power ARM1176JZFS Applications Processor

**GPU**Dual Core VideoCore IV® Multimedia Co-Processor

Provides Open GL ES 2.0, hardware-accelerated OpenVG, and

1080p30 H.264 high-profile decode

Capable of 1Gpixel/s, 1.5Gtexel/s or 24GFLOPs with texture filtering

and DMA infrastructure

**Memory** 512MB SDRAM

**Operating System** Boots from Micro SD card, running a version of the Linux operating

system

**Dimensions** 85 x 56 x 17mm

**Power** Micro USB socket 5V, 2A

**Connectors:** 

**Ethernet** 10/100 BaseT Ethernet socket

Video Output HDMI (rev 1.3 & 1.4)

Composite RCA (PAL and NTSC)

**Audio Output** 3.5mm jack, HDMI

**USB** 4 x USB 2.0 Connector

**GPIO Connector** 40-pin 2.54 mm (100 mil) expansion header: 2x20 strip

Providing 27 GPIO pins as well as  $+3.3\ V$ ,  $+5\ V$  and GND supply lines

Camera Connector 15-pin MIPI Camera Serial Interface (CSI-2)

JTAG Not populated

**Display Connector** Display Serial Interface (DSI) 15 way flat flex cable connector

with two data lanes and a clock lane

Memory Card Slot SDIO