


Raspberry Pi



Raspberry Pi 2, Model B

Product Name Raspberry Pi 2, Model B

Product Description The Raspberry Pi 2 delivers 6 times the processing capacity of previous models. This second generation Raspberry Pi has an upgraded Broadcom BCM2836 processor, which is a powerful ARM Cortex-A7 based quad-core processor that runs at 900MHz. The board also features an increase in memory capacity to 1Gbyte.

Specifications

Chip	Broadcom BCM2836 SoC
Core architecture	Quad-core ARM Cortex-A7
CPU	900 MHz
GPU	Dual Core VideoCore IV® Multimedia Co-Processor Provides Open GL ES 2.0, hardware-accelerated OpenVG, and 1080p30 H.264 high-profile decode Capable of 1Gpixel/s, 1.5Gtexel/s or 24GFLOPs with texture filtering and DMA infrastructure
Memory	1GB LPDDR2
Operating System	Boots from Micro SD card, running a version of the Linux operating system
Dimensions	85 x 56 x 17mm
Power	Micro USB socket 5V, 2A

Connectors:

Ethernet	10/100 BaseT Ethernet socket
Video Output	HDMI (rev 1.3 & 1.4)
Audio Output	3.5mm jack, HDMI
USB	4 x USB 2.0 Connector
GPIO Connector	40-pin 2.54 mm (100 mil) expansion header: 2x20 strip Providing 27 GPIO pins as well as +3.3 V, +5 V and GND supply lines
Camera Connector	15-pin MIPI Camera Serial Interface (CSI-2)
JTAG	Not populated
Display Connector	Display Serial Interface (DSI) 15 way flat flex cable connector with two data lanes and a clock lane
Memory Card Slot	Micro SDIO