# SNM022A-06 - Capsule Slip Rings

# SNM022A-06


Body Diameter: 22.00mm, Length: 19mm

6 circuits\*2A version


The SNM012A-06, with 6 wires and compact 22.00mm body diameter, which we call our "medium", uses SenRing's fiber brush technology which offers several advantages over conventional slip ring contacts including multiple points of contact per brush bundle, low contact force per fiber and low contact wear rates.



### **SNM022A-06 Dimensions**



## Flange mounted:



## SNM022A-06 Specifications

Contact Material	Gold alloy brush,Gold plated rings			
Current Rating	2A, per ring, maximum			
Number of Circuits	6			
Operating Speed	250 rpm* continuous			
Housing Material	Engineering Plastics			
Lead Wire	UL Teflon® Awg28,color-coded, silver-plated			
Lead Lengths	250mm			
Voltage	210 VDC / 240 VAC			
Operating Temp.	-40°C to 80°C			
Torque	Approx. ≤0.3 g·m (for reference )			
Dielectric Strength	≥600V@50Hz between each circuit			
Insulation Resistance	600MΩ@ 300VDC			
Noise	20 milliohms maximum tested @ 6 VDC, 40 milliamps when running @ 5 - 15 rpm			
Resistance to pull	Radial 2KG,Axial 0.5KG			
Protection	IP51			

\*Please note that the operational life of the unit is dependent upon rotational speed, environment

#### **Features**

- Gold-on-gold contacts
- Compatible with data bus protocols
- Transfers analog and digital signals, Ethernet, USB, RS, Canbus, Fire wire signal.
- Speeds up to 250 rpm continuous
- Precision ball bearings meet or exceed life requirements for most commercial applications
- Smooth running, Low torque, Compact dimemsions

### **Type Application**

- CCTV pan / tilt camera mounts | control equipment
- Electrical test equipment | Laboratory equipment
- Manufacturing and process | rotary index tables
- Medical equipment | Robotics
- Miniature cable reels

#### **Lead Wire Color Code**

Circuit No.	1	2	3	4	5	5
Color	BLK	BROWN	RED	ORG	YEL	GREEN