SNM022A-12 - Capsule Slip Rings

SNM022A-12

Body Diameter: 22.00mm, Length: 26mm


12 circuits * 2A version

The SNM022A-12, with 12 wires and compact 22.00mm body diameter, which we call our "medium",uses SenRing's fiber brush technology which offers several advantages over conventional slip ring contacts including multiple points of contact per brush bundle, low contact force per fiber and low contact wear rates.




SNM022A-12 Dimensions

SNM022A-12 Specifications



Flange mounted:



Contact Material Gold alloy brush, Gold plated rings Current Rating 2A, per ring, maximum **Number of Circuits Operating Speed** 250 rpm* continuous **Housing Material Engineering Plastics** Lead Wire UL Teflon® Awg28,color-coded, silver-plated Lead Lengths 250mm 210 VDC / 240 VAC Voltage Operating Temp. -40°C to 80°C Approx. ≤0.39 g·m (for reference) Torque Dielectric Strength ≥600V@50Hz between each circuit Insulation Resistance 600MΩ@ 300VDC

*Please note that the operational life of the unit is dependent upon rotational speed, environment and temperature.

when running @ 5 - 15 rpm

Radial 2KG, Axial 0.5KG

15 milliohms maximum tested @ 6 VDC, 40 milliamps

Features

- Gold-on-gold contacts
- Compatible with data bus protocols
- Transfers analog and digital signals, Ethernet, USB, RS, Canbus, Fire wire signal.
- Speeds up to 250 rpm continuous
- Precision ball bearings meet or exceed life requirements for most commercial applications
- Smooth running, Low torque, Compact dimemsions

Type Application

- Electrical test equipment | Laboratory equipment
- Manufacturing and process | rotary index tables
 - Medical equipment | Robotics

 Miniature cable reels

Lead Wire Color Code

Noise

Protection

Resistance to pull

Color BLACK BROWN RED ORANGE YELLOW GREEN Circuit No. 7 8 9 10 11 12	Circuit No.	1	2	3	4	5	5
	Color	BLACK	BROWN	RED	ORANGE	YELLOW	GREEN
Color DINE DIDDLE OPEY WHITE DINE HOLITON	Circuit No.	7	8	9	10	11	12
COIOT BLUE PURPLE GREY WHITE PINK LIGHT BLU	Color	BLUE	PURPLE	GREY	WHITE	PINK	LIGHT BLUE